



**General Specification**  
 Current Rating: 1.6A DC /Contact, 20mA DC for LED signals  
 Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals  
 Operating Environment: -20°C~+70°C  
 Standard Temperature: -40°C~+85°C  
 Industrial Temperature: -40°C~+85°C  
 Humidity: 20~70%  
 Contact Resistance: ≤30mΩ  
 Insulation Resistance: ≥500MΩ  
 Dielectric Strength: 500V AC/(50HZ) /Min  
 Mating And Unmating Force: 3~20N  
 Durability: 750 Cycles Min

**Material Specification**  
 Housing :Thermo-plastic, UL94V-0.  
 Contact :Alloy Copper  
 Shield :Alloy Copper  
 Please refer to the customer drawing when customer has specified

序号	名称	材料	数量	镀层/颜色	备注
4	外壳	HS2	1	NI	
3	LED灯	树脂/FE	2	NI/AG	
2	插针	PHOSPHOR BRONZE	8	1U"	
1	塑座	PA46	1	BLACK	

**网络插座外形图**



**温州瑞川电子有限公司**  
 WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

图号:	日期:	审核:	日期:	审核:	日期:
日期: 2022.4.20	日期:	日期:	日期:	日期:	日期:
变更单号:	变更历史:	变更单号:	变更历史:	变更单号:	变更历史:
版本:	版本:	版本:	版本:	版本:	版本:
A/0	新出版发行	A/0	新出版发行	A/0	新出版发行