

Specification Sheet

Part Number: 157-00402



Mount provides low insertion and high extraction forces which makes for a strong and easy installation.

Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.

Clamping rails increase grip on round bundles.

Thinner strap provides increased flexibility for improved ergonomics.

Wide Strap Cable Tie with .25" Stud Mount, 15.7" Long, 0.5" Wide, PA66HIRHSUV, Black, 300/bg

Article Number 157-00402

Type WSR250

Color Black (BK)

Quantity Per bag

Product Description
The Wide Strap Stud Mount Cable Tie minimizes pinching on soft bundles and features a low profile head to provide compact bundling. A thinner strap provides increased flexibility for improved ergonomics. Available in various stud mount sizes, the wide strap tie utilizes a strong hinge between the stud mount and head to provide superior holding ability on a threaded stud.

Short Description
Wide Strap Cable Tie with .25" Stud Mount, 15.7" Long, 0.5" Wide, PA66HIRHSUV, Black, 300/bg

Global Part Name WSR250-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 120.0

Minimum Tensile Strength (Metric) 535

Length L (Imperial) 15.7

Length L (Metric) 398.8

Fixation Method Stud Mount

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.5

Width W (Metric) 12.7

Bundle Diameter Min (Imperial) 0.38

Bundle Diameter Min (Metric) 9.5

Bundle Diameter Max (Imperial) 4.13

Bundle Diameter Max (Metric) 105.0

Thickness T (Imperial)	0.06
Thickness T (Metric)	1.4
Stud Diameter (Metric)	M6
Stud Diameter (Imperial)	1/4
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	300
Package Quantity (Metric)	300
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)