



Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Temperature range:-40°C~+125°C
 温度范围: -40°C~+125°C

K 137635 T F - P SN
 ① ② ③ ④ ⑤ ⑥

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:T-Terminal
- 4.Special No:F-Female Terminal
- 5.Material:P-Phosphor Bronze
- 6.Palting:SN-Plated Tin



SEC:A-A



SEC:B-B

K137635TF-PSN	Phosphor Bronze	AWG#28~24	K137635HM-B
PART NO	Material	Wire Range	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 2.2mm automotive connector
DWN	VIEW:	PART NO.: K137635TF-PSN
CHKD	UNIT: mm/in	DWG NO.: X-K137635TF-PSN
APPD	SIZE: A4	WEIGHT SHEET REVISION



XKB INDUSTRIAL PRECISION CO.,LIMITED

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES