



Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:20A AC/DC

额定电流: 20A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-40℃-+125℃

温度范围: -40℃-+125℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

K 838100 T F - B SN
① ② ③ ④ ⑤ ⑥

1.K: XKBTEK-Car Connector

2.XKB Series No

3.Category:T-Terminal

4.Special No:F-Female Terminal

5.Material:B-Brass

6.Plating:SN-Plated Tin

K838100TF-BSN	Brass	AWG#22~16	K838100HM
PART NO	Material	Wire Range	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 8.38mm Automobile connector
DWN	VIEW:	PART NO.: K838100TF-BSN
CHKD	UNIT: mm/in	DWG NO.: X-K838100TF-BSN
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0

XKB

XKB INDUSTRIAL PRECISION CO., LIMITED

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
					UNSPECIFIED TOLERANCES	
REVISIONS						
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						