



5	HOUSING	1	HIGH TEMP.THERMOPLASTIC	Black
4	TERMINAL 4#	1	COPPER ALLOY t=0.20	SEE TABLE
3	TERMINAL 3#	1	COPPER ALLOY t=0.20	SEE TABLE
2	TERMINAL 2#	2	COPPER ALLOY t=0.20	SEE TABLE
1	TERMINAL 1#	1	COPPER ALLOY t=0.20	SEE TABLE
No.	PART NAME	QTY	MATERIAL(THICK)	PLATING(COLOR)

SPECIFICATIONS:

1. ELECTRICAL CHARACTERISTICS:

- 1-1. RATING: 20V, 1A Min.
- 1-2. CONTACT RESISTANCE:
50 MILLIOHMS Max. FOR INITIAL,
80 MILLIOHMS Max. AFTER 5000 CYCLES.
- 1-3. INSULATION RESISTANCE: 100 MEGAOHMS Min.
BY 500V DC AFTER 1 MINUTE.
- 1-4. DIELECTRIC WITHSTANDING VOLTAGE: 500V
RMS AFTER 1 MINUTE.

2. MECHANICAL CHARACTERISTICS:

- 2-1. INSERTION FORCE : 0.3~3.0 KGf(2.94~29.4N)
- 2-2. WITHDRAWAL FORCE : 0.3~3.0 KGf(2.94~29.4N)

3. LIFE TEST: 5,000 CYCLES MIN.

广东星坤科技股份有限公司

Δx	日期
Δx	日期
Δx	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
-----------	------	---------	----------	------------------------

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5



DSND	SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
DWN	VIEW:	PART NO.: PJ-3528S
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED		WEIGHT
		SHEET
		REVISIC
		1/1
		A0