



SPECIFICATION

Contact Rating: 50mA, 12V DC
 Contact Resistance: 100MΩ max
 Insulation Resistance: 100MΩ min. 500V DC
 Dielectric Strength: 250V AC/1minute
 Travel: 0.15mm
 Operating Temp: -30°C ~ +85°C
 Storage Temp: -30°C ~ +80°C

PAPT NO	TS-1010A-X
Operating Force	A:100gf B:160gf C:260gf
Height	H:3.5

ITEM	PAPT NAMF	TER.NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Lcp	—	—
②	Cover	—	1	Brass	Plating Nickel	—
①	Keystake	—	1	LCP	—	—

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGLAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5
	REVISIONS				
	www.helloxkb.com www.helloxkb.cn www.xk-dg.cn				

XKKB INDUSTRIAL PRECISION CO., LIMITED

DSND

DWN

CHKD

APPD

SCALE: N/A

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE:
TACT SWITCH

PART NO.:
TS-1010A-X

DWG NO.:

WEIGHT

SHEET

REVISIC

1/1

A0