





| DATE     | SYM | REVISION RECORD  | AUTH | DR.  | CK. |
|----------|-----|--|------|------|-----|
| 03/24/17 | C   | ADDED DIM. 61.30<br>DIM. 55.10 WAS 55.00<br>DIM. 14.50 WAS 15.50 | T.B. | B.S. |     |
| 04/21/17 | D   | UPDATED SPECIFICATION  | T.B. | B.S. |     |
| 03/07/19 | E   | UPDATED TO "ROHS<br>COMPLIANT"                                   | T.B. | B.S. |     |



Note: Dimensions in mm. ( inches )

### SPECIFICATIONS :

Plastic material - polypropylene  
 Flammability Rating-UL94 HB, UL File No. E216959  
 Temperature Range: -10°C to +100°C  
 Springs - nickel plated spring steel  
 Rivets - Brass, nickel plated  
 Lugs - Brass, nickel plated  
 Contact Resistance: Under 50m for +/- contacts per EIA-540J000  
 ROHS COMPLIANT

|                                |   |                          |  |
|--------------------------------|---|--------------------------|--|
| Tolerance<br>(Except as noted) |  <b>Memory Protection Devices, Inc</b><br>200 Broad Hollow Road, Farmingdale, New York 11735 |                          |  |
| decimal<br>±.5 (.020)          | Scale   | Drawn By B.S.            |  |
| Fractional<br>± .8 (.030)      | Title<br>FOUR "AA" CELL HOLDER WITH SOLDER LUGS   |                          |  |
| Angular<br>± 3°                | Date<br>03/07/19  | Drawing Number<br>BC4AAL |  |
|                                |   | Approved By T.B.         |  |