# XS230SANAL2

Inductive proximity sensors XS, inductive sensor XS2 M30, L63mm, stainless, Sn22mm, 12...24 VDC, cable 2 m





#### Main

Range of Product	Telemecanique Inductive proximity sensors XS
Series name	Application
Sensor Type	Inductive proximity sensor
Device Application	Food and beverage
Market Segment	Pharmaceutical
Sensor name	XS2
Sensor design	Cylindrical M30
Size	63 mm
Body type	Fixed
Detector flush mounting acceptance	Non flush mountable
Material	Stainless steel
Type of output signal	Discrete
Wiring Technique	3-wire
[Sn] nominal sensing distance	0.87 in (22 mm)
Discrete output function	1 NO
Output circuit type	DC
Discrete output type	NPN
Electrical connection	Cable
Cable length	6.56 ft (2 m)
[Us] rated supply voltage	1224 V DC reverse polarity protection
Switching capacity in mA	<= 200 mA overload and short-circuit protection
IP degree of protection	IP68 double insulation conforming to IEC 60529 IP69K conforming to DIN 40050

#### Complementary

and the state of t		
Thread type	M30 x 1.5	
Detection face	Frontal	
Front material	PPS	
Enclosure Material	Stainless steel 316 L	
Sensing range	> 0.591.57 in (> 1540 mm)	
Operating zone	0.000.69 in (017.6 mm)	
Differential travel	115% of Sr	
Cable composition	3 x 0.34 mm <sup>2</sup>	
Wire insulation material	PVC	
Status LED	Output state 1 LED yellow)	
Supply voltage limits	1036 V DC	
Switching frequency	<= 500 Hz	
Maximum voltage drop	<2 V closed)	
Current consumption	<= 10 mA no-load	
Maximum delay first up	10 ms	
Maximum delay response	0.6 ms	
Maximum delay recovery	1.4 ms	

Marking	CE
Threaded length	1.61 in (41 mm)
Length	2.48 in (63 mm)
Net Weight	0.45 lb(US) (0.205 kg)

#### Environment

Product Certifications	UL CSA
Ambient Air Temperature for Operation	-13185 °F (-2585 °C)
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)
Vibration resistance	25 gn +/- 2 mm 1055 Hz)IEC 60068-2-6
Shock resistance	50 gn 11 ms IEC 60068-2-27

#### Ordering and shipping details

<u>-                                    </u>		
Category	22486-SENSORS, PROXIMITY	
Discount Schedule	DS2	
GTIN	3389119113304	
Nbr. of units in pkg.	1	
Package weight(Lbs)	7.05 oz (200.0 g)	
Returnability	No	
Country of origin	FR	

# Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.65 in (4.2 cm)
Package 1 width	3.74 in (9.5 cm)
Package 1 Length	5.31 in (13.5 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	1
Package 2 Weight	7.05 oz (200.0 g)
Package 2 Height	1.38 in (3.5 cm)
Package 2 width	9.84 in (25 cm)
Package 2 Length	7.87 in (20 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	11
Package 3 Weight	5.35 lb(US) (2.425 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)


## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS  Declaration
Mercury free	Yes
RoHS exemption information	₽¥Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Warranty 18 months

# **Dimensions Drawings**


#### **Dimensions**



# XS230SANAL2


#### Minimum Mounting Distances in mm

#### Side by side




e (1) ≥ 120 mm/4.72 in.

#### Face to face



e (2) ≥ 264 mm/10.39 in. Facing a metal object




- e (3)  $\geq$  66 mm/2.60 in.
- (4) Metal
- (5) Object to be detected

## Product data sheet Connections and Schema

# XS230SANAL2

### Wiring Schemes

NPN



BU : Blue BN : Brown BK : Black