


PCB. 焊接图



电路图

主要技术规格:

1. 额定值: 50mA DC12V
2. 接触电阻: $\leq 100m\Omega$
3. 操作力: $260 \pm 50gf$
4. 行程: $0.25 \pm 0.10mm$
5. 绝缘电阻: $\geq 100M\Omega$
6. 抗电强度: 100V 50HZ 1Min.
7. 寿命: 100,000 Cycles

材料:

- 本体: LCP (灰色)
- 按钮: 黄铜 (酸洗)
- 卡件: 磷铜 (镀银)
- 弹片: 不锈钢 (镀银)
- 盖板: 不锈钢
- 防水层: 聚酰亚胺

PAPT NO	TS1187A-X-X	
Operating Force	160 : 160gf ; 260 : 260gf	
Height	15:1.5mm	35 : 3.5mm
	16:1.6mm	40 : 4.0mm
	17:1.7mm	45 : 4.5mm
	20:2.0mm	50 : 5.0mm
	25 : 2.5mm	
	30 : 3.0mm	

		new		2015/5/3	A	瀚源
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	TS1187A-X-X	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ± 0.25
			MODEL NAME	TS1187A-X-X		X.xx ± 0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xxx ± 0.15
					ANGULAIR	± 3
					FILE.NO.	