



电路图



- 1.Contact; MechanicalCo
- 2.Rating; Dc12v50mA
- 3.Travel; 0.15 ± 0.3 MM
- 4. Operating Force: 250 ± 50 gf
- 5.Contact Resistance; $100 \text{ m}\Omega$
Max
- 6.Life; 100 000 Cycles Mim

PAPT NO	TS1179S-X-X
Operating Force	160 : 160gf ; 260 : 260gf
Height	43:4.3mm 50 : 5.0mm

		new		2015/5/3	A	瀚源
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	TS1179S-X-X	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ±0.25
			MODEL NAME	TS1179S-X-X		X.x ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15
					ANGULAIR	±3
					FILE.NO.	