




- 主要技术规格:**
1. 额定值: 50mA DC12V
 2. 接触电阻: 100mΩ
 3. 操作力: 250±50gf
 4. 行程: 0.12±0.1mm
 5. 绝缘电阻: 100MΩ
 6. 抗电强度: 250V 50HZ 1Min.
 7. 寿命: 7万次

材料:
 本体:LCP (原色)
 按钮:PPA (白色)
 卡件: 磷铜 (镀银)
 弹片: 不锈钢 (镀银)
 盖板: 磷铜 (镀铜锡)



PAPT NO	TS1145-X-X
Operating Force	160 : 160gf ; 260 : 260gf
Height	25 : 2.5mm



		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	TS1145-X-X	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25		
			MODEL NAME	TS1145-X-X		X.x	±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	±0.15	ANGULAIR	±3