

Ass'y High(H)	Plastic High	
	Male (H1)	Female (H2)
8.00	6.90	6.00
10.00	8.90	6.00


**SPECIFICATIONS**  
**PERFORMANCE**  
 Current Rating (信号端子) : 0.5A  
 Current Rating (电源端子) : 5A  
 Contact Resistance: 80mΩMax  
 Insulation Resistance: 500MΩMin  
 Withstand Volt: 200V AC/minute  
 Opratng Temperature: -40°C to +105°C

**Material**  
 Contact: Phosphor Bronze, 3u" MIN Gold Plated In Contact Area,  
 Gold Flash Plated In Solder Area,  
 50u"~240u" Nickel Underplated Over all.  
 Ground: Brass, 80u" Min Matte Tin Plated Over  
 50u" Min Nickel Underplated Over all.  
 Housing: LCP Black, UL94V0  
 Max.Processing Temp: 230°C for 30~60 seconds  
 (260°C for 10 seconds)

PIN	A	B	C	D	E
30 Pin	19.60	8.50	7.00	12.80	17.50
50 Pin	24.60	13.50	12.00	17.80	22.50
60 Pin	27.10	16.00	14.50	19.30	25.00
80 Pin	32.10	21.00	19.50	24.30	30.00
100 Pin	37.10	26.00	24.50	29.30	35.00
120 Pin	42.10	31.00	29.50	34.30	40.00

**Ordering Information**  
 HC-PBB23L - NDP - 0.5V \* - \*\* - 01

No. of Pins: 30~120Pin, 30~30Pin, 50~50Pin, ...  
 Nature DP=Male  
 PITCH: 0.5V=0.5mm  
 High (H): 8=8.0mm, 10=10.0mm  
 Contact Plating: G2:3u" Gold, S2:1u" Gold/Tin, S1:3u" Gold/Tin, S2:5u" Gold/Tin, S3:10u" Gold/Tin, S4:15u" Gold/Tin, S5:30u" Gold/Tin



			GENREL TOLERANCE	制图 DRAWING	<b>深圳市华灿天禄电子有限公司</b> ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK	产品名称 TITLE	BTB 0.5 高频大电流 浮动式 贴片公座	版本 REV.	A
			X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	HC-PBB23L-NDP-0.5VX-XX-01	单位 UNITS	mm
			X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10	投影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					