

产品编号 : 1053860003

Product Description : Reinforced, Anti-Snag Spring Clip, 1.00mm Width, 0.25µm Gold (Au) Plating, 0.40mm - 0.80mm Working Range (Height)

系列号 : 105386


状态 : New Business Not Supported

Product Category : Connector Accessories

文件和资源

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

多部分产品合规性声明

- Eu RoHS
- REACH SVHC
- Low-Halogen

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

欧盟 RoHS 合格证书

产品详情

常规

状态	New Business Not Supported
类别	Connector Accessories
系列	105386

说明	Reinforced, Anti-Snag Spring Clip, 1.00mm Width, 0.25 μ m Gold (Au) Plating, 0.40mm - 0.80mm Working Range (Height)
元件类型	Clip
产品系列	Spring Clips for Mobile Devices
产品名称	Spring Clip
UPC	889056228824

电气

每触点最大电流	1.5A
---------	------

物理

回路数（已载入）	1
电路数（最多）	1
材料 - 金属	Stainless Steel
材料 - 接合部位电镀	金牌
材料 - 终端电镀	金牌
净重	0.033/g
包装形式	Embossed Tape on Reel
最薄镀层 - 接合部位	0.254 μ m
运行温度范围	-40° to +85° C
终端界面类型	Solder