

SAKQ 2.5/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

| | |
|---------------|--|
| Version | Cross-connector (terminal), when screwed in, Number of poles: 10, Pitch in mm (P): 5.50, Insulated: No |
| Order No. | 1129300000 |
| Type | SAKQ 2.5/10 |
| GTIN (EAN) | 4032248996155 |
| Qty. | 20 pc(s). |
| Local product | Only available in certain countries |

Creation date April 29, 2024 8:46:58 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

SAKQ 2.5/10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General ordering data

| | |
|---------------|-------------------------------------|
| Local product | Only available in certain countries |
|---------------|-------------------------------------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 13.5 mm | Depth (inches) | 0.531 inch |
| Height | 54 mm | Height (inches) | 2.126 inch |
| Width | 6 mm | Width (inches) | 0.236 inch |
| Net weight | 11.95 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

System specifications

| | |
|---------------|----|
| PE connection | No |
|---------------|----|

Additional technical data

| | |
|----------------|-----------------|
| Type of fixing | when screwed in |
|----------------|-----------------|

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 5.5 mm |
|-----------------|--------|

General

| | |
|-----------------|----|
| Number of poles | 10 |
|-----------------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |