



PCB LAYOUT

Specifications:

规格:
Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
Current rating:3A AC/DC
 额定电流: 3A AC/DC
Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
Temperature range:-40°C~+105°C
 温度范围: -40°C~+105°C
Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
Material:PA6T UL94V-0
 材质: PA6T UL94V-0
Plating Category:1U"Gold
 镀层: 1U"Gold
Wave soldering temperature:255±5°C, 10S
 波峰焊温度: 255±5°C, 10S

X6521 W V - 2xXX H - C60 D30
 ① ② ③ ④ ⑤ ⑥ ⑦

1. Series No
2. Category:W-Wafer
3. Welding Board Angle:V-Stright 180°
4. Row No.Pin No:2xXX-2x01~2x40P
5. Plastic Height:H=2.5mm
6. Pin Length:C=6.0mm
7. Pin Length:D=3.0mm

X6521WW-2xXXH-C60D30	PA6T	Brass	X6521F
PART NO	Material	Material(Pin)	Suitable XKB Female

广东星坤科技股份有限公司
 文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ#					ANGLAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.54mm BTB Connector
DWN		VIEW:	PART NO.: X6521WW-2xXXH-C60D30
CHKD		UNIT: mm/in	DWG NO.: X-X6521WW-2xXXH-C60D30
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0