


Specifications

Coupling: Threaded coupling
 Shell material: Brass with Nickel Plate
 Insert material: bakelite
 Contact material: copper Silver Plate/Nickel
 Termination: Solder
 Mating cycle: 500
 Cable diameter: -20°C +85°C


Ordering Information

XD - GX12 - NP - *


No. of Pin
2-7 Pin
Contact
Type
F=Female
M=Male




2P




3P




4P



5P



6P



7P

NO. of contacts	芯数	2	3	4	5	6	7
Rated current (A)	额定电流	5A	5A	5A	5A	5A	5A
Operation limit voltage(AC.V.rms)	工作电压(AC.V)分钟	200V	125V	125V	125V	125V	125V
Withstanding voltage(AC.V.rms) 1 minute	耐电压	1500	1500	1500	1500	1500	1500
Insulation resistance (mΩ)	绝缘阻抗	2000	2000	2000	2000	2000	2000
Contact resistance (mΩ)	接触阻抗	5	5	5	5	5	5
Solder cup mouth aperture	焊杯口径φ(mm)	φ0.8	φ0.8	φ0.8	φ0.8	φ0.8	φ0.8
Solder inter diameter	接触体孔径φ(mm)	φ1.2	φ1.2	φ1.2	φ1.2	φ1.2	φ1.2

GENERAL TOLERANCE			制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			审核 CHECK	产品名称 TITLE	GX12 航空插头 公头	版本 REV.	A
			批准 APPROVAL	产品料号 PART NO.	XD-GX12-NP-M	单位 UNITS	mm
1	初版发行		比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	投影 Projection				