


Specifications

Coupling: Threaded coupling  
 Shell material: Zinc alloy with Nickel Plate  
 Insert material: bakelite  
 Contact material: copper Silver Plate/Nickel  
 Termination: Solder  
 Mating cycle: 500  
 Cable diameter: -20°C +85°C



Ordering Information

XD - GX20 - NP - \*

└───┬───┘

No. of Pin  
2-10 Pin

└───┬───┘

Contact  
Type  
F=Female  
M=Male

NO. of contacts	芯数	2	3	4	5	6	7	8	9	10	12	14	15
Rated current (A)	额定电流	15A	15A	10A	10A	10A	10A	10A	10A	5A	5A	5A	5A
Operation limit voltage(AC.V.rms)	工作电压(AC.V)分钟	250V	250V	200V	200V	200V	200V	200V	200V	200V	200V	200V	200V
Withstanding voltage(AC.V.rms) 1 minute	耐电压	1500	1500	1500	1000	1000	1000	1000	1000	1000	1000	1000	1000
Insulation resistance(mΩ)	绝缘阻抗	1500	1500	1500	1000	1000	1000	1000	1000	1000	1000	1000	1000
Contact resistance (mΩ)	接触阻抗	3	3	3	3	3	3	3	3	3	3	3	3

			GENERAL TOLERANCE	制图 DRAWING	<b>深圳讯答科技有限公司</b> ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	GX20 航空插头 母头	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XD-GX20-NP-F	单位 UNITS	mm
			X.XXX ±0.10		投影 Projection	材料 MATERIAL		页次 SHEET
1	初版发行		Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						