


Specification Sheet

Part Number: 170-20600



Nylon monofilament construction weave offers a tight braid that provides full coverage but will not rot or retain moisture.

Material performs well in wet applications and where abiding substrate has a smooth surface.

Helagaine Braided Sleeving, 6 mm Dia, PA66,GY, 328ft/Reel

Article Number 170-20600

Type HEGPA6606

Color Gray (GY)

Quantity Per metre

Product Description Helagaine Nylon Polyamide Expandable Braided Sleeving is a pliable yet durable sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.

Short Description Helagaine Braided Sleeving, 6 mm Dia, PA66,GY, 328ft/Reel

Global Part Name HEGPA6606-PA66-GY

Length L (Imperial)	328.0
Length L (Metric)	100.0
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4
Bundle Diameter Max (Imperial)	0.32
Bundle Diameter Max (Metric)	8
Diameter D (Imperial)	0.24
Diameter D (Metric)	6.1
Nominal Diameter (Imperial)	0.25
Nominal Diameter (Metric)	6
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	FMVSS 302 UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No

Operating Temperature -76°F to +302°F (-60°C to +150°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 328

Package Quantity (Metric) 100

Customs Number 5808100000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)