

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A		NEW		22.3.4

NOTES1:

UL Standard

1. Rated voltage/current : 150V / 8A
2. Withstanding voltage : AC1250V/1Min.

IEC Standard

1. Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	2.5KV
Rate voltage(V)	320V
Rate current(A)	10A

NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009
2. Pitch : 2.54mm, Poles : N=04~48P
3. Operating temperature: -40°C~+105°C
4. Undimensioned tolerances:






Pitch range in mm		Nominal dimension range in mm					0.1/10	□
TO	Over	TO	Over	Over	Over	0.1/10		
6	6 TO 10	30	30 TO 60	60	60 TO 100	100	150	±2'
	±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30

5. RoHS Compliance

Ordering Information

JL15EDGVHDM-254 XX B 0 1

- Pitch 254=2.54PH
- No. of pins 4P~48P
- Housing Color: B=Black, G=Green, U=Blue, R=Red, W=White, Y=Yellow, O=Orange, E=Grey
- Packing: 0=Pe bag, T=Tube, A=Tray



PCB LAYOUT

DRAW	SHUANGPING ZHENG	SCALE	FIT	东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
		UNIT	mm		
CHECK	LICHAO LIU	SIZE	A4		
		SHEET	1/1		
APPROVE	YONGLIANG GAO	PROJ.		PART NO.	JL15EDGVHDM-254XXB01
		TITLE:	JL15EDGVHDM-THR-2.54-2XNP 插拔式公座/带耳/直针/黑色		