


Specification Sheet

Part Number: 151-00757

Suitable for applications with minimal space.

CTAM has 4-way entry design for use in line or at 90° angle to cable run.

CTAM mounts are available in different sizes and materials.



Cable Tie Anchor Mount, 0.17" Hole Dia, 0.20" Max Tie Width, PEEK, Beige, 100/pkg

Article Number 151-00757

Type CTAM1

Color Beige (BGE)

Quantity Per bag

Product Description Anchor Mounts for cable ties are suitable for applications with minimal space. Anchors are mounted onto the equipment prior to cable installation and take up no more space than the cable itself. Choose between a four-way entry design that can be used either 'in line' or at 90 degrees to the cable run.

Short Description Cable Tie Anchor Mount, 0.17" Hole Dia, 0.20" Max Tie Width, PEEK, Beige, 100/pkg

Global Part Name CTAM1-PEEK-BGE

Length L (Imperial)	0.81
Length L (Metric)	20.5
Fixation Method	Screw Mount
Width W (Imperial)	0.4
Width W (Metric)	10.2
Cable Ties	T18 - T50
Height H (Imperial)	0.22
Height H (Metric)	5.5
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Mounting Hole Diameter D (Imperial)	0.17
Mounting Hole Diameter D (Metric)	4.3 mm
Mounting Hole Diameter D Max (Metric)	4.3
Material	Polyetheretherketone (PEEK)
Material Shortcut	PEEK

Flammability	UL 94 V-0
UV Resistant (Yes/No)	No
Operating Temperature	-67°F to +464°F (-55°C to +240°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)