

乐清市博穆电子有限公司

XHB 条形连接器 (2.54mm)

技术参数 TECHNICAL PARAMETER

间距(PITCH):2.54mm

极数(Poles):2--15

适用基板厚度(Applicable PC board thickness):1.6mm

额定电流(Current rating):5A,AC,DC

额定电压(Voltage rating):250V,AC,DC

工作温度(Working Temperature):-25℃~+85℃

耐压值(Withstand voltage):1500V,AC/min

接触电阻(Contact resistance): $\leq 0.01 \Omega$

绝缘电阻(Insulation resistance): $\geq 1000M \Omega$

极数 Poles	编号 Part Number		尺寸 Dimensions(mm)	
			A	B
2	XHB-2A	XHB-2AW	2.54	7.5
3	XHB-3A	XHB-3AW	5.08	10
4	XHB-4A	XHB-4AW	7.62	12.5
5	XHB-5A	XHB-5AW	10.16	15
6	XHB-6A	XHB-6AW	12.7	17.5
7	XHB-7A	XHB-7AW	15.24	20
8	XHB-8A	XHB-8AW	17.78	22.5
9	XHB-9A	XHB-9AW	20.32	25
10	XHB-10A	XHB-10AW	22.86	27.5
11	XHB-11A	XHB-11AW	25.4	30
12	XHB-12A	XHB-12AW	27.94	32.5
13	XHB-13A	XHB-13AW	30.48	35
14	XHB-14A	XHB-14AW	33.02	37.5
15	XHB-15A	XHB-15AW	35.56	40

材料 MATERIAL

基座(HOUSING):尼龙66UL94V-0(NYLON66 UL94V-0)

插针(PIN):黄铜(BRASS)表面镀纯锡(PURE TIN-PLATED)

