


SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C ~ +85°C
4. Contact Resistance: 30mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 650V AC/minute
7. Material: Wafer Nylon66 UL94-V0(2)
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-XHD-2x2A-05	2.50	7.50
3	HC-XHD-2x3A-05	5.00	10.00
4	HC-XHD-2x4A-05	7.50	12.50
5	HC-XHD-2x5A-05	10.00	15.00
6	HC-XHD-2x6A-05	12.50	17.50
7	HC-XHD-2x7A-05	15.00	20.00
8	HC-XHD-2x8A-05	17.50	22.50
9	HC-XHD-2x9A-05	20.00	25.00
10	HC-XHD-2x10A-05	22.50	27.50
11	HC-XHD-2x11A-05	25.00	30.00
12	HC-XHD-2x12A-05	27.50	32.50
13	HC-XHD-2x13A-05	30.00	35.00
14	HC-XHD-2x14A-05	32.50	37.50
15	HC-XHD-2x15A-05	35.00	40.00
16	HC-XHD-2x16A-05	37.50	42.50
17	HC-XHD-2x17A-05	40.00	45.00
18	HC-XHD-2x18A-05	42.50	47.50
19	HC-XHD-2x19A-05	45.00	50.00
20	HC-XHD-2x20A-05	47.50	52.50



			GENERAL TOLERANCE		制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审 核 CHECK					
			X, X	±0.30	批 准 APPROVAL		产品名称 TITLE	XHD (2.50) 双排直针	版本 REV.	A
			X, XX	±0.20	比 例 SCALE		产品料号 PART NO.	HC-XHD-2xNA-05	单 位 UNITS	mm
			X, XXX	±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°						