



NOTES:
 1. Material:
 Insulator: PBT+30%GF, UL 94V-0,
 Color: Black or Grey.
 2. Temperature Range: -25°C to +85°C

PART NO.
 Z-B810 ** 210000 * 1
 No. of Positions 10~64
 Color
 0=Black
 8=Grey
 9=White



| | | | | | |
|--|---------------------------|-------------------|--|----------------------|----|
| UNITS: <input checked="" type="checkbox"/> mm <input type="checkbox"/> inch SIZE: A3 NAME: 2.54MM CRIMP TYPE IDC HOUSING | | | TOLERANCE LEVEL (UNLESS OTHERWISE SPECIFIED) B | | |
| A (ISO2768-m) | | | B | | |
| RANGE | mm | DEFINED TOLERANCE | PART NO: Z-B810**210000*1 | | |
| 0 ~ 6 | ± 0.1 | .X ± 0.38 | APPD: Peter廖小瓊 2023/11/16 | | |
| 6 ~ 30 | ± 0.2 | .XX ± 0.25 | CHKD: Peter廖小瓊 2023/11/16 | | |
| 30 ~ 120 | ± 0.3 | .XXX ± 0.08 | DRAW: | | |
| 120 ~ 400 | ± 0.5 | | DESIGN: Lily寶麗星 2023/11/15 | | |
| ANGLE | X° ± 1° | ANGLE | X° ± 2° | TITLE: CUSTOMER DWG. | |
| REV. DESCRIPTION DATE | | | DWG NO: 010-0000-F48 | | |
| A2 | UPGRADE VERSION ECR-23042 | 2023/10/18 | SCALE SHEET REV. | | |
| A1 | MODIFY | 2018/08/17 | NA | 1/1 | A2 |

CONFIDENTIAL: THIS DOCUMENT CONTAINED THE INFORMATION IS PROPRIETARY AND CONFIDENTIAL TO Nexttronics Engineering Corp. NO PERSON IS ALLOWED TO USE COPY, PUBLISH OR OTHERWISE DISCLOSE THE INFORMATION TO OTHERS, UNLESS BY THE PRIOR WRITTEN EXPRESS AUTHORIZATION OF Nexttronics Engineering Corp. (C)COPYRIGHT- Nexttronics Engineering Corp.

USE SHOWN DIMENSIONS DO NOT SCALE DRAWING