



NOTES:
 1. Material:
 Insulator: PBT+30%GF, UL 94V-0,
 Color: Black or Grey.
 2. Temperature Range: -25°C to +85°C

PART NO.
 Z-B810 ** 210000 * 1
 No. of Positions 10~64
 Color
 0=Black
 8=Grey
 9=White



REV.	DESCRIPTION	DATE
A2	UPGRADE VERSION ECR-23042	2023/10/18
A1	MODIFY	2018/08/17

UNITS: <input checked="" type="checkbox"/> mm <input type="checkbox"/> inch		SIZE: A3	NAME:
TOLERANCE LEVEL (UNLESS OTHERWISE SPECIFIED)		B	2.54MM CRIMP TYPE IDC HOUSING
A (ISO2768-m)		B	
RANGE	mm	DEFINED TOLERANCE	PART NO:
0 ~ 6	± 0.1	.X	± 0.38
6 ~ 30	± 0.2	.XX	± 0.25
30 ~ 120	± 0.3	.XXX	± 0.08
120 ~ 400	± 0.5		
ANGLE	X° ± 1°	ANGLE	X° ± 2°
DESIGN: Lily 寶麗星			2023/11/15
APPD: Peter 廖小瓊			2023/11/16
CHKD: Peter 廖小瓊			2023/11/16
DRAW:			
TITLE:			CUSTOMER DWG.
DWG NO:			010-0000-F48
SCALE	SHEET	REV.	
NA	1/1	A2	

CONFIDENTIAL: THIS DOCUMENT CONTAINED THE INFORMATION IS PROPRIETARY AND CONFIDENTIAL TO Nexttronics Engineering Corp.
 NO PERSON IS ALLOWED TO USE COPY, PUBLISH OR OTHERWISE DISCLOSE THE INFORMATION TO OTHERS, UNLESS BY THE PRIOR
 WRITTEN EXPRESS AUTHORIZATION OF Nexttronics Engineering Corp. (C)COPYRIGHT- Nexttronics Engineering Corp.

USE SHOWN DIMENSIONS
 DO NOT SCALE DRAWING