



TYPE 1



PCB LAYOUT

SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C ~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-XH-2AW-X	2.50	7.50
3	HC-XH-3AW-X	5.00	10.00
4	HC-XH-4AW-X	7.50	12.50
5	HC-XH-5AW-X	10.00	15.00
6	HC-XH-6AW-X	12.50	17.50
7	HC-XH-7AW-X	15.00	20.00
8	HC-XH-8AW-X	17.50	22.50
9	HC-XH-9AW-X	20.00	25.00
10	HC-XH-10AW-X	22.50	27.50
11	HC-XH-11AW-X	25.00	30.00
12	HC-XH-12AW-X	27.50	32.50
13	HC-XH-13AW-X	30.00	35.00
14	HC-XH-14AW-X	32.50	37.50
15	HC-XH-15AW-X	35.00	40.00
16	HC-XH-16AW-X	37.50	42.50

Ordering Information

HC-XH - N*** - *

Pin Type Colour

A=直针 G=白色(加强)

M=弯针 B=米色

ALT=空脚 R=红色

AW=空脚 L=蓝色

 B=黑色

 P=紫色

GENERAL TOLERANCE			制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
DIM	TOL	审 核 CHECK	批 准 APPROVAL		产 品 名 称 TITLE	版 本 REV.	A	
X.X	±0.30				产 品 料 号 PART NO.	XH(TJC3) 弯针	单 位 UNITS	mm
X.XX	±0.20				比 例 SCALE	HC-XH-NAW-X	页 次 SHEET	1/1
X.XXX	±0.10				投 影 Projection			
Angle	±3.0°				材 料 MATERIAL			
1	初版发行	日期 MODIFY DATE						
序号 No.	变更内容 MODIFY CONTENT							