



PCB Layout (Pattern side)



Note:
1. Rating: 12V 50mA

NO.1			
PART NO	H	PART NO	H
XX	4.3	XX	13.0
XX	4.5	XX	13.5
XX	5.0	XX	14.0
XX	5.5	XX	14.5
XX	6.0	XX	15.0
XX	6.5	XX	15.5
XX	7.0	XX	16.0
XX	7.5	XX	16.5
XX	8.0	XX	17.0
XX	8.5	XX	17.5
XX	9.0	XX	18.0
XX	9.5	XX	18.5
XX	10.0	XX	19.0
XX	10.5	XX	19.5
XX	11.0	XX	20.0
XX	11.5		
XX	12.0		
XX	12.5		

NO.2	
PART NO	vigor
1	70±30
2	100±50
3	160±50
4	260±50
5	320±80
6	350±80
7	520±130

⑤	Terminal	4	Brass(0.30t)	Plating silver
④	Contact	1	F.Ag/SUS	—
③	Base	1	Nylon	Black
②	Cover	1	SPCC	Plating Nickel
①	Keystoke	1	Nylon	Black
ITEM	PART NAME	QTY.	MATERIAL	FINISHING

APPROVALS		DATE
DRAWN	G.M.Chen	2014/8/18
CHECKED		
APPROVALS		

DEALON 德之隆®
ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	DRAWING NO.	PROJ.
	A		NEW				30~PL: ±0.30 10~30 ±0.20 5~10 ±0.15 ~ 5 ±0.10	±2'		
							TITLE: TACT SWITCHES			
							PART NO. TD-1101SR-XXH-XXX			
							UNIT: mm SCALE: 1:1		SHEET 1 OF 1	
							DRAWING NO.		PROJ. ①	