





FILE: 02/

Kinghelm®



REV	CONTENT	CHK	DATE
V0.0	CONTENT		2014-11-20



- NOTES:
1. Rating: 300V 15A ;
 2. Insulation Withstands Voltage: AC2000V/MIN
 3. Insulation Resistance: 500MΩ or more at DC500V
 4. Using Temperature Range: -40°C~+105°C
 5. "★" is the important dimension



SECTION:A-A



DIM	2	3	4	5	6	7	8	9	10	xxx	24
L	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	xxx	121.92
A	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	xxx	116.84

Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	≡	-	//								
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 500	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150	0.2	0.3	0.3	0.2	0.3	0.5
±0.18	? 0.20	±0.25	±0.3	±0.35	? 0.44	±0.60	±0.70	? 0.85		±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90													

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	DATE	2014-11-20	SIZE	A4 UNITS mm	SHEET/OF 1 / 1
CHK.	DATE		SCALE	3:1	5.08
APP.	DATE		NAME		
深圳市金航标电子有限公司		www.kinghelm.com.cn	DWGNO		
KH-F400V-3P-5.08G		0755-28190160			