





FILE: 02/

Kinghelm®



REV	CONTENT	CHK	DATE
V0.0	CONTENT		2014-11-20



- NOTES:
1. Rating: 300V 15A ;
 2. Insulation Withstands Voltage: AC2000V/MIN
 3. Insulation Resistance: 500MΩ or more at DC500V
 4. Using Temperature Range: -40°C~+105°C
 5. "★" is the important dimension



SECTION:A-A



DIM	2	3	4	5	6	7	8	9	10	xxx	24
L	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	xxx	121.92
A	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	xxx	116.84

Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	≡	-	//				
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 500	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	over 100	over 150				
to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500		to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320		to 100	to 150						
±0.18	? 0.20	±0.25	±0.3	±0.35	? 0.44	±0.60	±0.70	? 0.85		±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90		0.2	0.3	0.3	0.2	0.3	0.5		

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	DATE	2014-11-20	SIZE	A4 UNITS mm	SHEET/OF 1 / 1
CHK.	DATE		SCALE	3:1	5.08
APP.	DATE		NAME		
深圳市金航标电子有限公司		www.kinghelm.com.cn	DWGNO		
KH-F400V-9P-5.08G		0755-28190160			