





Kinghelm®



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

SPECIFICATION

- 1 Material:
 Insulator: PA66 (UL94V-0)
 Contacts: Brass, Gold-plated
- 2 Contact resistance: ≤20mΩ
- 3 Insulation resistance: ≥1000MΩ
- 4 Rated voltage: 250 V AC DC
- 5 Rated current: 2.5 A AC DC
- 6 Withstand Voltage: 800V AC/minute
- 7 Temperature Range: -25℃ ~ +85℃
- 8 Six deleterious substance content meet the environmental protection requirement

				TOLERANCE *,* ±0.25 *,** ±0.15 *,*** ±0.05		SCALE: UNIT: mm VIEW:		<h1>2510-A</h1>	
				DRAW		CHECK		TITLE: 2.54mm PITCH 90° WAFER	
				APPRO				PART NO: 深圳市金航标电子有限公司 www.kinghelm.com.cn	
REV	DESCRIPTION	REV. DRAWN	DATE					KH-HX2.54-10Z 0755-28190160	
A	NEW RELEASE								