

1次molding (7.35带弹有柱)






Kinghelm®

REV	DESCRIPTION	DATE	APPROVED
A0	初版发行	2019.06.27	TSQ


NOTES:

SPECIFICATION:

- CURRENT RATING: 5A MAX
- VOLTAGE: 100 VAC
- TEMPERATURE RANGE: -30 °C ~ 85 °C
- CONTACT RESISTANCE: 40 MILLIONHM MAX
- INSULATION RESISTANCE: 100 MEGOHMS MIN.
- INSERTION FORCE : 5N~20N
- UNMATING FORCE: 8N~20N
- DURABILITY: 5000 CYCLES



CONNECTOR FRONT EDGE
RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
6	SHELL	STAINLESS STEEL	Ni/SN Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS

TOLERANCESIZE: x. ± 0.10 . X ± 0.05 . XX ± 0.04 . XXX ± 0.02	TITLE : Typec贴板母座-16Pin	深圳市金航标电子有限公司	WWW.KINGHELM.COM.CN
	PART NO.	KH-TYPE-C-T	0755-28190160
DWG NAME.	UNITS: MM	SCALE: 1:1	SIZE: A4
	SHEET: 1/1	PROJECTION:	REV: A0
	APPD: (核准)		