


| | | | | | | | | | |
|----------------------|---|---|---|---|------|-------------|---------------|---------|----------|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | | |
| Dept | 晨翔2.54mm FC三件式插头, 20PIN, 有上盖, 黑色胶芯, 半金镍端子 | | | | REV. | DESCRIPTION | DRAWN | CHECKED | APPROVED |
| Qty | | | | | A | NEW RELEASE | JLZ 12/01/21' | | |
| DC | 1 | | | | | | | | |
| ED | 1 | | | | | | | | |
| IE | 1 | | | | | | | | |
| ISO | 1 | | | | | | | | |
| PD | 1 | | | | | | | | |
| R&D | 1 | | | | | | | | |
| SD | 1 | | | | | | | | |
| QA | 1 | | | | | | | | |
| QC | 1 | | | | | | | | |
| QF | 1 | | | | | | | | |
| 晨翔料号: DS1016-20MA2BB | | | | | | | | | |

The information provided herein is from CONNELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNELY or its affiliates. Unauthorized use of this information in any format or manner. CONNELY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.



- 备注:
- 电性说明:
 - 1.1 接触阻抗: 20毫欧最大
 - 1.2 耐压: 500伏交流电一分钟
 - 1.3 绝缘阻抗: 1000兆欧最小
 - 1.4 额定电流: 3安
 - 环境特性:
 - 2.1 工作温度: -40~+105° C
 - 材料:
 - 3.1 端子: 黄铜, 接触区镍底镀金
 - 3.2 胶芯: PBT, 黑色, 阻燃

| | | | | | | | | |
|-------------------|-------|------------------|--------------|------------|---|--------|---------------------------|--|
| GENERAL TOLERANCE | | ANGLE TOLERANCE | | PROJECTION | | TITLE | I.D.C SOCKET PITCH 2.54mm | |
| X. | ±0.60 | X. | ±5° | UNITS | mm | SERIES | DS1016 SERIES | |
| .X | ±0.38 | .X | ±3° | SHEET SIZE | A4 | | | |
| .XX | ±0.25 | .XX | ±2° | | | | | |
| DRAWING TYPE | | CUSTOMER | | | 晨翔电子有限公司 CONNELY CONNELY ELECTRONIC CO. LTD | | | |
| SCALE | | 1:1 | SHEET 1 OF 1 | | | | | |
| DRAWING NO. | | C-DS1016-XXXXX-A | | | | | | |