




1	2	3	4	5	6	7	8	
Dept	晨翔2.54mm IC母座, 24P, DIP, 黑色胶芯, 脚距7.62宽, 有杠, 端子镀锡			REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
Qty				A	NEW RELEASE	JLZ 06/18/24'	~	
DC	晨翔料号:DS1009-24AT1NS-0A2							
ED								
IE								
ISO								
PD								
R&D								
SD								
QA								
QC								
QF								

The information provided herein is from CONNELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNELY or its affiliates. Unauthorized use of this information in any format or manner. CONNELY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.



- 备注:
- 电性说明:
    - 接触阻抗: 30毫欧最大
    - 耐压: 600伏交流电一分钟
    - 绝缘阻抗: 1000兆欧最小
    - 额定电流: 1安
  - 环境特性:
    - 工作温度: -40~+105° C
  - 材料:
    - 端子: 磷铜, 镍底镀锡
    - 胶芯: PBT, 黑色, 阻燃



PCB孔位尺寸参考  
公差: ±0.05

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.54mm IC SOCKET
X.	±0.60	X.	±5°	UNITS	mm		Stamping Type
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1009 SERIES
.XX	±0.25	.XX	±2°	<b>晨翔电子有限公司</b> <b>CONNELY CONNELY ELECTRONIC CO. LTD</b>			
DRAWING TYPE		CUSTOMER					
SCALE		1:1 SHEET 1 OF 1					
DRAWING NO.		C-DS1009-XXXX-XXX-A					