


1	2	3	4	5	6	7	8	
Dept	晨翔2.54mm IC母座, 24P, DIP, 黑色胶芯, 脚距15.24宽, 无杠, 端子镀锡			REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
Qty	1			A	NEW RELEASE	JLZ 06/18/24'	~	
DC	1							
ED	1							
IE	1							
ISO	1							
PD	1							
R&D	1							
SD	1							
QA	1							
QC	1							
QF	1							
晨翔料号:DS1009-24AT1WX-0A2								

The information provided herein is from CONNELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNELY or its affiliates. Unauthorized use of this information in any format or manner. CONNELY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.



- 备注:
- 电性说明:
 - 接触阻抗: 30毫欧最大
 - 耐压: 600伏交流电一分钟
 - 绝缘阻抗: 1000兆欧最小
 - 额定电流: 1安
 - 环境特性:
 - 工作温度: $-40 \sim +105^{\circ}C$
 - 材料:
 - 端子: 磷铜, 镍底镀锡
 - 胶芯: PBT, 黑色, 阻燃

PCB孔位尺寸参考
公差: ± 0.05

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.54mm IC SOCKET
X.	± 0.60	X.	$\pm 5^{\circ}$	UNITS	mm		Stamping Type
.X	± 0.38	.X	$\pm 3^{\circ}$	SHEET SIZE	A4	SERIES	DS1009 SERIES
.XX	± 0.25	.XX	$\pm 2^{\circ}$	晨翔电子有限公司 CONNELY CONNELY ELECTRONIC CO. LTD			
DRAWING TYPE		CUSTOMER					
SCALE		1:1					
DRAWING NO.		C-DS1009-XXXXX-XXX-A		SHEET		1 OF 1	