



SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Housing Nylon66 UL94-V0(2)

Circuit	Part NO.	Dimensions mm			
		A	B	C	D
2	HC-HY-2Y	2.00	5.50	3.20	4.55
3	HC-HY-3Y	4.00	7.50	3.20	6.55
4	HC-HY-4Y	6.00	9.50	4.30	8.55
5	HC-HY-5Y	8.00	11.50	4.30	10.55
6	HC-HY-6Y	10.00	13.50	8.30	12.55
7	HC-HY-7Y	12.00	15.50	10.30	14.55
8	HC-HY-8Y	14.00	17.50	12.30	16.55
9	HC-HY-9Y	16.00	19.50	12.30	18.55
10	HC-HY-10Y	18.00	21.50	12.30	20.55
11	HC-HY-11Y	20.00	23.50	16.30	22.55
12	HC-HY-12Y	22.00	25.50	16.30	24.55
13	HC-HY-13Y	24.00	27.50	16.30	26.55
14	HC-HY-14Y	26.00	29.50	16.30	28.55
15	HC-HY-15Y	28.00	31.50	16.30	30.55
16	HC-HY-16Y	30.00	33.50	16.30	32.55
19	HC-HY-17Y	32.00	35.50	16.30	34.55
18	HC-HY-18Y	34.00	37.50	16.30	36.55
17	HC-HY-19Y	36.00	39.50	16.30	38.55
20	HC-HY-20Y	38.00	41.50	16.30	40.55

			GENERAL TOLERANCE		制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK					
			X.X	±0.30	批 准 APPROVAL		产品名称 TITLE	HY (2.0) 单排孔座	版本 REV.	A
1			初版发行		比 例 SCALE		产品料号 PART NO.	HC-HY-NY	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1