


SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C ~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer LCP, UL94-V0  
PIN Brass Tin-plated  
Solder pad Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-HY-2ALT	2.00	8.00	4.90
3	HC-HY-3ALT	4.00	10.00	6.90
4	HC-HY-4ALT	6.00	12.00	8.90
5	HC-HY-5ALT	8.00	14.00	10.90
6	HC-HY-6ALT	10.00	16.00	12.90
7	HC-HY-7ALT	12.00	18.00	14.90
8	HC-HY-8ALT	14.00	20.00	16.90
9	HC-HY-9ALT	16.00	22.00	18.90
10	HC-HY-10ALT	18.00	24.00	20.90
11	HC-HY-11ALT	20.00	26.00	22.90
12	HC-HY-12ALT	22.00	28.00	24.90
13	HC-HY-13ALT	24.00	30.00	26.90
14	HC-HY-14ALT	26.00	32.00	28.90
15	HC-HY-15ALT	28.00	34.00	30.90
16	HC-HY-16ALT	30.00	36.00	32.90
17	HC-HY-17ALT	32.00	38.00	34.90
18	HC-HY-18ALT	34.00	40.00	36.90
19	HC-HY-19ALT	36.00	42.00	38.90
20	HC-HY-20ALT	38.00	44.00	40.90

Ordering Information

HC-HY - N\*\*\* - \*



			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	HY (2.0) 单排立贴	版本 REV.	A
			X.XX	±0.20	比例 SCALE		产品料号 PART NO.	HC-HY-NALT	单位 UNITS	mm
			X.XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°							