





- SPECIFICATIONS
1. Current Rating: 2A AC, DC
  2. Voltage Rating: 250V AC, DC
  3. Temperature Range: -25°C ~ +85°C
  4. Contact Resistance: 20mΩ Max
  5. Insulation Resistance: 1000mΩ Min
  6. Withstanding Voltage: 1000V AC/minute
  7. Material: Wafer LCP UL94-V0(2)  
PIN Brass Tin-plated  
Solder pad Brass Tin-plated

Circuit	Part No.	Dimensions mm			
		A	B	C	D
2	HC-HY-2AWT	2.00	8.00	4.90	2.50
3	HC-HY-3AWT	4.00	10.00	6.90	2.50
4	HC-HY-4AWT	6.00	12.00	8.90	3.50
5	HC-HY-5AWT	8.00	14.00	10.90	5.50
6	HC-HY-6AWT	10.00	16.00	12.90	7.50
7	HC-HY-7AWT	12.00	18.00	14.90	9.50
8	HC-HY-8AWT	14.00	20.00	16.90	11.50
9	HC-HY-9AWT	16.00	22.00	18.90	13.50
10	HC-HY-10AWT	18.00	24.00	20.90	15.50
11	HC-HY-11AWT	20.00	26.00	22.90	17.50
12	HC-HY-12AWT	22.00	28.00	24.90	19.50
13	HC-HY-13AWT	24.00	30.00	26.90	21.50
14	HC-HY-14AWT	26.00	32.00	28.90	23.50
15	HC-HY-15AWT	28.00	34.00	30.90	25.50
16	HC-HY-16AWT	30.00	36.00	32.90	27.50
17	HC-HY-17AWT	32.00	38.00	34.90	29.50
18	HC-HY-18AWT	34.00	40.00	36.90	31.50
19	HC-HY-19AWT	36.00	42.00	38.90	33.50
20	HC-HY-20AWT	38.00	44.00	40.90	35.50



			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	HY (2.0) 单排卧贴	版本 REV.	A
			X.XX	±0.20	比例 SCALE		产品料号 PART NO.	HC-HY-NAWT	单位 UNITS	mm
			X.XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°							