

SPECIFICATIONS

Mechanical

Contact Retention Force: 0.10kg min.
Durability : 60 Cycles

Electrical

Voltage Rating: 25V
Current Rating: 0.5A
Contact Resistance: 60mΩ max.
Dielectric Withstanding Voltage: 250V AC/1 min.
Insulation Resistance: 100MΩ

Physical


Housing: Thermoplastic, UL 94V-0 rated in Ivory Color
Contact: Copper alloy
Plating: See "ORDERING INFORMATION"
Metal Spring: Copper alloy
Operating Temperature: -55°C to +85°C

DDRIV SO DIMM Socket

AS Series
5.2 mm Height
SMT Type
0.50mm Pitch
260 Pos.



DRAWING



ORDERING INFORMATION

PRODUCT NO.: **A S O A8 2 * - H 2 * B - * H**

Memory Module Socket
 Horizontal Type
 Single Row
 No. Of Pos.
 A8=260 Pos.
 SMT Type
 Contact Area Plating
 1=Gold Flash
 Y=5u"Gold Plating
 6=10u"Gold Plating
 7=15u"Gold Plating
 3=30u"Gold Plating

H=HALOGEN /LEAD FREE
 Package Code
 4=Soft Tray
 7=Tape Reel
 B=BLACK COLOR
 S=Standard
 R=Reverse
 2=5.2mm Height
 H=DDR SODIMM

| | | |
|------------------|-------|-------|
| AS0A82*-H2SB- *H | 35.50 | 28.50 |
| AS0A82*-H2RB- *H | 28.50 | 35.50 |
| P/ N | DIM.A | DIM.B |