



2:1

RoHS compliant
by exemption

1727040148	FMP007P103	103
1727040187	FMP007P105	105
1731121205	FMP007P106	106
1731120841	FMP007P110	110
1731120042	FMP007P203	203
Material Number	FCT Part Number	Material + Finish See extra sheet

UNLESS OTHERWISE SPECIFIED DIMENSIONS FOR REFERENCE ONLY				REPLACEMENT FOR DOCUMENT NUMBER: FMP007P								
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
FUNCTIONAL SYMBOLS	DIMENSION UNITS	SCALE	CURRENT REV DESC:									
$\frac{F}{A} = 0$	mm	5:1	EC NO: 686935 DRWN: FVETTER 2021/11/29 CHK'D: MTEUBEL 2021/11/30 APPR: MTEUBEL 2021/11/30									
$\frac{F}{E} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)											
$\frac{F}{P} = 0$	ANGULAR TOL ± °											
DIVISIONAL SYMBOLS	4 PLACES	±										
	3 PLACES	±	INITIAL REVISION:									
	2 PLACES	±	DRWN: VLOKESHA 2021/03/31									
	1 PLACE	±	APPR: MTEUBEL 2021/11/25									
	0 PLACES	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		FIRST ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	DOC TYPE	DOC PART	REVISION
						A4-SIZE	172704	SEE TABLE	GENERAL MARKET	PSD	000	A1

molex
FCT 40A HIGH POWER CONTACT
FOR D-SUB

PRODUCT CUSTOMER DRAWING
DOCUMENT NUMBER: 1727040148
DOC TYPE: PSD
DOC PART: 000
REVISION: A1