



NOTE:
 1.MATERIAL:FPC PCB 106.7mm*13mm
 THICKNESS:
 PSA:3M 467
 Pl:50um
 BASE COPPER:18-20um
 2.TOLERANCE ON ALL COPPER ARTWORK IS +/-0.05MM.
 3.TOLERANCE ON ALL DIE CUTLINES IS +/-0.10MM.
 4.TOLERANCE BETWEEN ARTWORK AND DIE CUTLINES IS +/-0.15MM.
 5.Ni & Au PLATING ON SOLDER PADS ONLY
 Ni:1-3um
 Au:Min. 0.10um THICKNESS
 6.COVER COAT:BLACK
 7.PRINT TEXT
 COLOR:WHITE,
 TEXT HEIGHT:1.5MM

PART NUM	① FLEX	② CABLE	DIM. A
1052630001	1052631001	1052631004	95.15MM
1052630002	1052631001	1052631005	145.15MM
1052630003	1052631001	1052631006	195.15MM

ENTER DESCRIPTION EC NO:ABU2014-0057 DRWN:ZLRAO 2014/4/21 CHKD:RANDY 2014/4/21 APPR:CHRIS 2014/4/21	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE METRIC ONLY	SCALE 1:1	DESIGN UNITS MM	THIRD ANGLE PROJECTION		
		4 PLACES ±	3 PLACES ±	2 PLACES ±	1 PLACE ±	0 PLACE ±	DRAWN BY DATE ZLRAO 2014/4/21		
		ANGULAR ± °					CHECKED BY DATE RANDY 2014/4/21		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					APPROVED BY DATE CHRIS 2014/4/21		
B1	REV	SEE TABLE			MATERIAL NO.	DOCUMENT NO. SD-105263-001	SHEET NO. 1 OF 1		

