





MATERIAL:
 HOUSING: PA46, PBT, PA66, BLACK.
 TERMINAL: PHOSPHOR BRONZE 00.46MM
 GOLD PLATING

SHIELD: C2680, T=0.20MM, 20 MIN NICKEL PLATING
 NO ALL AREA

DURABILITY: 750 CYCLES MIN. 12.5MM/MINUTE.
 INSERTION FORCE: 2.2KG.F MAX.
 RETENTION STRENGTH: 7.7KG.F BETWEEN JACK AND PLUG.
 OPERATING TEMPERATURE: -40°C~+85°C.
 STORAGE TEMPERATURE: -40°C~+85°C.
 ALL CRITICAL DIMENSIONS WITH "M"

VOLTAGE: 125 VOLTS AC.
 CURRENT RATING: 1.5AMP.
 DIELECTRIC STRENGTH: 1000 VAC RMS 50HZ OR 60HZ, 1MIN.
 INSULATION RESISTANCE: 500 MEGA OHMS MIN. INITIAL
 AFTER 500V DC FOR 1 MINUTE.
 CONTACT RESISTANCE: SINGLE TERMINAL 30 MILLIOHMS MAX.
 INITIAL 50 MILLIOHMS MAX. AFTER
 DURABILITY TEST.



			GENREL TOLERANCE		制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD					
			DIM	TOL	审 核 CHECK							
			X. X	±0.30	批 准 APPROVAL		产品名称 TITLE	网络插座 (无灯带弹)	版本 REV.	A		
1			初版发行		X. XX		±0.20	产品料号 PART NO.	HC-RJ45-059C-2*2-3	单 位 UNITS	mm	
序号 No.			变更内容 MODIFY CONTENT		日 期 MODIFY DATE		Angle	±3.0°	投 影 Projection	材 料 MATERIAL	页 次 SHEET	1/1