



| | | | | | TOLERANCE UNLESS SPECIFIED | | | | | | | |
|-----|--------------|----------|-----|------------|-------------------------------|----------------|----|------------|-----------|-------|----------|-----------|
| | | | | | UP TO 5mm: ±0.1 | ANGULAR ±1° | | | | | | |
| | | | | | ABOVE 5mm: ±0.2 | | NO | DATE | REVISIONS | | BY | APPD |
| 4 | CONTACT FOOT | BRASS | 1 | Sn-Plating | TITLE: DIN SOCKET | | | UNIT : MM | ROHS | DWN | Hunter.H | 2010-1-12 |
| 3 | CONTACT FOOT | BRASS | 5 | Sn-Plating | MODEL: DIN-504 | | | SCALE: 1:1 | COMPLIANT | CHK'D | LSU,S | 2010-1-12 |
| 2 | COVER | PBT | 1 | | 东莞市六钧电子五金有限公司 | | | APPD | | ZHU,S | | 2010-1-12 |
| 1 | HOUSING | PBT | 1 | | | | | | | | | |
| NO. | PART NAME | MATERIAL | QTY | FINISHING | | | | PRO.AGL: | | | | REV : A |