





NOTES

1. 材質及びめっき仕様
MATERIAL AND FINISH

部品 PART	材質 MATERIAL
ターミナル TERMINAL	銅合金 COPPER ALLOY
	コンタクト部：金めっき 0.1 micro-meters MIN CONTACT AREA: GOLD PLATING 0.1 micro-meters MIN
	バレル部：無光沢錫めっき 1.0micro-meter MIN BARREL AREA : MATTE TIN PLATING 1.0micro-meter MIN
	ニッケルめっき(下地) 1.0 micro-meter MIN NICKEL PLATING (UNDER PLATING) 1.0 micro-meter MIN

2. 適用製品及び各種仕様書はSHEET 2を参照のこと
REFER TO SHEET 2 ABOUT APPLICABLE PRODUCTS
AND VARIOUS SPECIFICATIONS



∅0.5-0.7	AWG #28-30	5037650098	CHAIN
INS RANGE	WIRE RANGE	ORDER NO	FORM

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: REDRAWN AND REVISED		molex			
DIMENSION UNITS	SCALE						
mm	NTS			PRODUCT CUSTOMER DRAWING			
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 640538		DOCUMENT NUMBER			
ANGULAR TOL ± 3.0 °		DRWN: QHE31 2018/03/14		5037650000-SD			
4 PLACES ± 0.2		CHK'D: SAKIYAMA 2020/07/06		DOC TYPE DOC PART REVISION			
3 PLACES ± 0.2		APPR: KOMURAKAMI 2020/07/07		PSD 000 A			
2 PLACES ± 0.2		INITIAL REVISION:					
1 PLACE ± 0.2		DRWN: QHE31 2018/03/14					
0 PLACES ± 0.2		APPR: KOMURAKAMI 2020/07/07					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			A3-SIZE	503765	SEE CHART		1 OF 2

△ 適用製品及び各種仕様書
 APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS

梱包仕様書 PACKAGING SPECIFICATION	PART NUMBER 5037650098	DOCUMENT NUMBER SPK-503765-001
----------------------------------	---------------------------	-----------------------------------

適用ハウジング APPLICABLE HOUSING	SINGLE TYPE
----- シリーズ番号 SERIES No	503764

適合嵌合相手 MATE WITH	SMT
	GOLD PLATING
	RIGHT ANGLE
----- シリーズ番号 SERIES No	503763
製品仕様書 PRODUCT SPECIFICATION	PS-503764-001
アプリケーション仕様書 APPLICATION SPECIFICATION	AS-503764-001

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
DIMENSION UNITS	SCALE	CURRENT REV DESC: REDRAWN AND REVISED					molex			
mm	NTS						PICO-LOCK1.0 REC CRIMP TERM AWG#28-30			
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 640538 DRWN: QHE31 2018/03/14 CHK'D: SAKIYAMA 2020/07/06 APPR: KOMURAKAMI 2020/07/07 INITIAL REVISION: DRWN: QHE31 2018/03/14 APPR: KOMURAKAMI 2020/07/07					PRODUCT CUSTOMER DRAWING			
ANGULAR TOL ± 3.0 °							DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
4 PLACES ± 0.2							5037650000-SD	PSD	000	A
3 PLACES ± 0.2										
2 PLACES ± 0.2										
1 PLACE ± 0.2										
0 PLACES ± 0.2										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER				
		A3-SIZE	503765			2 OF 2				