

Crimpingtools see document 2195600660
Cable RG179BU, RG187AU

1731120576	FMS002P101	101
1727040128	FMS002P102	102
1731121066	FMS002P202	202
Material Number	FCT Part Number	Material + Finish See extra sheet


Crimpingtools:
Crimping of inner conductor:

Hand tool: 1731121730
Locator: 1731121738

Pneumatic crimp tool: WA22
Locator: 1731121738

Cable:
AWG 24 / SEL. 5
AWG 26 / SEL. 5
AWG 28 / SEL. 4
AWG 30 / SEL. 3

Cable trimming
dimensions



RoHS compliant
by exemption

UNLESS OTHERWISE SPECIFIED DIMENSIONS FOR REFERENCE ONLY				REPLACEMENT FOR DOCUMENT NUMBER: FMS002P			
FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:				
	DIMENSION UNITS	SCALE	EC NO: 730943				
$\frac{E}{A} = 0$	mm	5:1	DRWN: SUGEEB 2022/07/07				
$\frac{E}{E} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		CHK'D: MTEUBEL 2022/12/06				
$\frac{E}{P} = 0$	ANGULAR TOL ± °		APPR: MTEUBEL 2022/12/06				
DIVISIONAL SYMBOLS	4 PLACES	±	INITIAL REVISION:				
	3 PLACES	±	DRWN: SUGEEB 2022/07/07				
	2 PLACES	±	APPR: MTEUBEL 2022/12/06				
	1 PLACE	±	DOCUMENT NUMBER				
0 PLACES	±	1731120576					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		FIRST ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			A4-SIZE	173112	SEE TABLE	GENERAL MARKET	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2022/12/06	14:05:23
-----------------	----	--------------	------------	----------