



产品编号 : 797580001

Product Description : Pre-Crimped Lead Mini-Fit Female-to-Mini-Fit Female, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Red

系列号 : 79758

状态 : Active

Product Category : Power and Signal Cable Assemblies


文件和资源

图纸

图纸 [797580001_sd.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

多部分产品合规性声明

- Eu RoHS
- REACH SVHC
- Low-Halogen
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

欧盟 RoHS 合格证书

产品详情

常规

状态	活动
类别	Power and Signal Cable Assemblies
系列	79758
说明	Pre-Crimped Lead Mini-Fit Female-to-Mini-Fit Female, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Red
组件配置	Pre-crimped Lead Only
连接器到连接器	Mini-Fit Crimp Terminals
关键字	Pre-Crimped Leads
产品系列	Off-the-Shelf Pre-Crimped Leads
产品名称	Mini-Fit
UPC	884982052642

物理

电缆长度	150.00mm
回路数 (已载入)	1
电路数 (最多)	1
颜色-树脂	红色
性别	Female-Female
材料 - 金属	Brass
材料 - 接合部位电镀	Tin
材料 - 终端电镀	Tin
净重	1.628/g
包装形式	Bag
单端的	否
终端界面类型	Crimp or Compression
导线/电缆型号	UL 1061
线径规格 (AWG)	18

可连接使用部件

描述	产品编号
Mini-Fit BMI Dual Row Receptacle Housings	<u>42474</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>43760</u>

Mini-Fit BMI Dual Row Receptacle Housings	<u>44516</u>
Mini-Fit Jr. Receptacle Housings	<u>5557</u>

This document was generated on Jun 28, 2024