_	12		11	10		9	0		1	0	
		ERIAL MBER	ENGINE NUM								
н	1300	390376	DN1	50							
					I						
G											
F	━ 1.91 [48.4]									5-F	
							Ø1.00 [25	41			
E											
		(4)— (3)—									
	NOTE	S:									
D											
		FINISH: AS N									
	3.	3. ELECTRICAL:									
		VOLTAGE: 50 VAC/VDC									
с	4.	CURRENT: 8 AMPS 4. TEMP RATING: 0°C TO +60°C									
))						
	7.										
	TOLERANCED OR NOTED OTHERWISE									PRE-RELEASE REFERENCE USE ONL	
В		PRETERE									
	ITEM	COMPO	ONENT	MATE	RIAL	FIN	IISH			EUN	
	1	INSI	ERT	TP	Έ	GF	RAY	C		SY VA	
	2	CONTACT	SOCKET	COPPER	ALLOY	GOLD OV	ER NICKEL				
	3	COUPLI	NG NUT	ZINC DI	ECAST	BLACK E	-COATED				
A	4	OVER	MOLD	TP		GF	RAY	C		DIVI	
		RESIS	STOR	121 OH METAL F WA	ILM 1/4						
FC	DOCUMENT DRMAT: IN-ACAD-Ib-prod-C EVISION: B att: 2020/1/4	STATUS RV	RELEASE DATE		17:02:28	9	8	-	7	6	
DA	ATE: 2020/01/14		1 1	10		~	U		•	- ~	

