



Poles	Part No.	Dimension mm	
		A	B
2	2501S-2P	2.50	7.50
3	2501S-3P	5.00	10.00
4	2501S-4P	7.50	12.50
5	2501S-5P	10.00	15.00
6	2501S-6P	12.50	17.50
7	2501S-7P	15.00	20.00
8	2501S-8P	17.50	22.50
9	2501S-9P	20.00	25.00
10	2501S-10P	22.50	27.50
11	2501S-11P	25.00	30.00
12	2501S-12P	27.50	32.50
13	2501S-13P	30.00	35.00
14	2501S-14P	32.50	37.50
15	2501S-15P	35.00	40.00
16	2501S-16P	37.50	42.50

SPECIFICATIONS
 Current rating: 3A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20mΩ max.
 Withstand voltage: 1000V AC/min
 Insulation resistance: 1000MΩ/min.
 Temperature range: -25°C~+85°C
 Applicable PC board thickness: 0.063"(1.6)

Material:
 Part No: 2~16
 Post: Brass, Tin/plated
 Base: PA66 UL94V-2

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	CLIENT P/N			
CHECKED:	DATE:	UNIT	SCALE	REV.	FILE NO.
		mm	Free	A	Client#-2501-0002
DRAWN:	DATE:	SCALE			
LYP	2010-08-12	Free			
TITLE:		REV.			
2501S-XP 打K		A K1.00			
深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD					