



SIDE	DATE	DESCRIPTION	APPROVER
△			
△			

一、 MATERIAL:

1. Insulator: PBT+30%Glass Fiber (UL94V-0)
2. Contact: Brass
3. Contact Plated: Glod Flash over Tin Or Glod Plated Or Tin Plated
4. Shell: Stell, Nickel Plated

二、 SPECIFICATION:

1. Current Rating: 5 AMPS
2. Insulation Resistance: 1000MΩ MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C~+105° C.

		公差					
		.0±0.30	.0°±2.0°				
		.00±0.25	.00°±1.0°				
		.000±0.05	.000°±0.5°				
比例 (scale)	1 : 1	绘图 (draw)		单位 (units)	mm	图名 (name)	HDD-15M焊线
页次 (sheet)	A / 1	设计 (de'n)		颜色 (shaded)		图号 (draw number)	
版次 (rev.)	A / 0	审核 (ch'k)		材料 (mt'l)		料号 (Part number)	
视图 (view)		核准 (app'd)		处理 (finish)		图档 (File Name)	