

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	HP 21/06/05	~	LJC 21/06/05
B	整理图面	YCH 09/17/07	~	LJC 09/17/07
C	DRAWING UPDATE	JLZ 07/01/17'	~	

NOTES:




1. SPECIFICATIONS

- . Contact Resistance: 30mΩ max
- . Insulation Resistance: 1000MΩ min.
- . Current Rating: 1A
- . Dielectric withstanding voltage: AC 500V For 1 minute
- . Contact: Copper alloy.
- . Housing: Thermoplastic(UL 94V-0)

2. PRODUCT NUMBER CODE:

DS1091 - X X X X

- Screw type
X: W/O screw
S: W/ #4-40(UNC) screw
D: Rivet Type With Screw
In Bulk Package
- Contact plating
O: Selective gold flash
- Shell plating
N: Nickel
6: Tin
- Color of housing
W: WHITE
B: BLACK
V: Ivory



GENERAL TOLERANCE	ANGLE TOLERANCE
X. ±0.60	X. ±5°
.X ±0.38	.X ±3°
.XX ±0.25	.XX ±2°

PROJECTION	TITLE
UNITS	DVI PLUG WITH RIGHT ANGLE 24+5(JDR-245)
SHEET SIZE	SERIES DS1091

DRAWING TYPE	CUSTOMER
SCALE	1:1 SHEET 1 OF 1
DRAWING NO.	C-DS1091-XXXX-C

CONNFLY 晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO. LTD