







PRODUCT NO.	DSIC08TSGER
RoHS compliant	




NOTES :

- 1> Specification:
  - 1> Operating force: 1000gf Max
  - 2> Operating Temperature: -40° to +85°
  - 3> Storage Temperature: -40° to +85°
  - 4> Mechanical Life: 3000cycles minimum
  - 5> Electrical Life: 2000cycles 25mA 24VDC
2. PLATING:
  - GOLD FLASH 1u"(min.) SOLDER TAIL,
  - 3u" GOLD PLATING ON THE CONTACT AREA,
  - WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION

DSIC XX I S G E R

- [包装方式: T=管装 R=Reel]
- [电键层: B=接触面3u" G=接触面3u" P=接触面1.2u"]
- [G=镀金 S=内金小帽]
- [脚型: S脚 / J脚 / 直脚 / A脚 / Z脚]
- [T=低接触 S=低接触 L=长脚]
- [产品代码: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]



Number	Part Name	Material	Finished
①	Actuator	UL94 VO	White
②	Cover	UL94 VO	Black
③	Movable	Copper Alloy	3u"Gold
④	Terminal	Brass	1u"Gold
⑤	Base	UL94 VO	Black
⑥	Terminal Contact	Brass	3u"Gold
⑦	Mylar	UL94 VO	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES	PROJECTION	COPY
0 ± 0.25	0 ± 2'		
.00 ± 0.15	.0 ± 1'		
.000 ± 0.10	.00 ± 0.5'		
DESIGN	kathy	2012/04/12	
DRAWING			
CHECK			
APPRO.			

**KE** 东莞市广誉实业有限公司  
Dongguan Kingtek Industrial Co., Ltd.

FILE NO.	DSIC08TSGER-A
SIZE UNIT	SCALE SHEET REV.
A4	mm 2 : 1 1 OF 1 A