



料号 Part NO.	型号 Part NO.	尺寸 Dimensions				适用PCB板	
		H (mm)	A (mm)	B (mm)	W (mm)	钻孔	板厚
35-KWS-IN	KWS-IN	11.4	17.9	8.6	11.0	4.8	2.0



材质: UL 合格尼龙66;

颜色: 白色;

防火等级: 94V-2, 绝缘性不易老化。

用法: 基板钻孔4.8mm, 先把导线套固定。再将欲固定之导线放入套中, 从两侧轻轻一扣, 即可将导线牢牢扣住。可作任何与角度的固定电线之用。



未经并受权不得修改和复印  
该知识产属于技术质量部

DIMENSION	TOLERANCES	DWG. BY				CHK. BY		DATE
		A	NEW PART	REVISION RECORD	DWG. BY	CHK. BY	DATE	
0.0 0.00	±1.0				<i>alliuang</i>	<i>34 wang</i>	<i>2020/02</i>	
FIRST ANGLE PROJ		LTR.						

DWG. BY	UNIT	DWG. NO.
<i>liu liang</i>	mm	HIMA/QR-JZ-35-KWS-IN
CHK. BY	REV.	
<i>alliuang</i>	A	
APP. BY	DWG. NO.	
<i>wang yanyan</i>		

**HIMA** 惠华苏州惠华电子科技有限公司